

Technical data sheet

Cover, 90° bend A2

Item number: 6036982



Cover for 90° bend fitting for lockable and screw-on cable trays in indoor and outdoor areas, to protect cables against damage and soiling. Fastening with pre-mounted sash lock and through attachment of the section cover. Suitable for all side heights.
The cover can be used with fittings of all side heights.



A2 Stainless steel

2B Bright, treated

Master data

Item number	6036982
Type	RBD 90 600 A2
Description 1	Cover
Description 2	for 90° bend
Manufacturer	OBO
Dimension	B600mm
Colour	stainless steel
Material	Stainless steel 1.4301
Surface	Bright, treated
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	280 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	37,8115 kg CO2e / 1 Piece


Technical data sheet

Cover, 90° bend A2

Item number: 6036982



Dimensions



Length	657 mm
Width	600 mm
Plate thickness	1 mm
Dimension B	600 mm

Technical data

Bend (angle)	90°
Number of turn buckles	1 St.
Fastening type	Sash lock
Maintain electrical functions	no
Suitable for mesh cable tray	no
Suitable for cable ladder	no
Suitable for cable tray	yes
Change of direction	Horizontal
ROHS-conformant	yes
Rustproof steel, pickled	no
Hinged	no
Permitted temperature range, max.	120 °C
Permitted temperature range, min.	-20 °C