


# Technical data sheet

## T piece 60/400 A4

Item number: 6038186



T piece for the creation of a horizontal branch, fitting for lock and screw-on cable trays of side height 60 mm. Screwless mounting with double clamps or screw connection with FRS truss-head screws and M6 combination nuts. Can be used indoors and outdoors. Fastening material must be ordered separately.



|    |                 |
|----|-----------------|
| A4 | Stainless steel |
| 2B | Bright, treated |

### Master data

|                                    |                            |
|------------------------------------|----------------------------|
| Item number                        | 6038186                    |
| Type                               | RT 640 A4                  |
| Description 1                      | T piece                    |
| Description 2                      | for cable tray, horizontal |
| Manufacturer                       | OBO                        |
| Dimension                          | 60x400                     |
| Colour                             | stainless steel            |
| Material                           | Stainless steel 1.4571     |
| Surface                            | Bright, treated            |
| Surface standard                   |                            |
| Smallest sales unit                | 1                          |
| Unit of quantity                   | Piece                      |
| Weight                             | 293.9 kg                   |
| Weight unit                        | kg/100 pc.                 |
| CO2 Footprint (GWP) Cradle-to-Gate | 24,2627 kg CO2e / 1 Piece  |


# Technical data sheet

T piece 60/400 A4

Item number: 6038186



## Dimensions



|                 |        |
|-----------------|--------|
| Width           | 400 mm |
| Height          | 60 mm  |
| Plate thickness | 1 mm   |
| Dimension B     | 400 mm |

## Technical data

|                                         |                      |
|-----------------------------------------|----------------------|
| Connector version                       | Integrated connector |
| Maintain electrical functions           | yes                  |
| NATO hole pattern                       | no                   |
| ROHS-conformant                         | yes                  |
| Rustproof steel, pickled                | no                   |
| Permitted temperature range, max.       | 120 °C               |
| Permitted temperature range, min.       | -20 °C               |
| Wide-span version                       | no                   |
| Type of connector, cable support system | Screwed              |
| Recommended quantity of bolts           | 21 St.               |
| Rail thickness                          | 1.25 mm              |