


Technical data sheet

Magic bend, variable 110 FS

Item number: 6040680



Magic bend 0°–90°, variable, with quick connector system. For all cable tray types of 110 mm side height.



St	Steel
FS	Strip galvanised

Master data

Item number	6040680
Type	RBMV 110 FS
Description 1	Variable bend
Description 2	with quick connector
Manufacturer	OBO
Dimension	110x100
Colour	zinc
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	103.9 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	3,8944 kg CO2e / 1 Piece

Technical data sheet

Magic bend, variable 110 FS

Item number: 6040680



Dimensions



Width	100 mm
Height	110 mm
Plate thickness	1 mm
Dimension B	100 mm
Dimension L	340 mm

Technical data

Bend (angle)	Adjustable
Connector version	Integrated connector
Maintain electrical functions	no
Mounting perforation in base	yes
NATO hole pattern	no
Change of direction	Horizontal
ROHS-conformant	yes
Rustproof steel, pickled	no
Side perforation	yes
Wide-span version	no
Type of connector, cable support system	Click fastening