

Technical data sheet

90° angle connector for cable trays and ladders FS

Item number: 6043067



90° angle connector for the creation of a horizontal branch, suitable for latchable and screwable cable trays as well as screwable cable ladders with a 110 mm side height.

Screwless mounting with double clamps or screw connection with FRS truss-head screws and M6 combination nuts. Can be used in indoor areas. Fastening material must be ordered separately.



St

Steel

FS

Strip galvanised

Master data

Item number	6043067
Type	WKV 110 FS
Description 1	Angle connector
Description 2	for cable trays and ladders
Manufacturer	OBO
Dimension	110mm
Colour	zinc
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	5
Unit of quantity	Piece
Weight	21.86 kg
Weight unit	kg/100 pc.


Technical data sheet

90° angle connector for cable trays and ladders FS

Item number: 6043067



Dimensions



Dimension	190x110
Length	190 mm
Width	71 mm
Height	107 mm
Plate thickness	1.25 mm

Technical data

Quantity of bolts	0 St.
Version for	Angle connector
Maintain electrical functions	no
Suitable for mesh cable tray	no
Suitable for cable ladder	yes
Suitable for cable tray	yes
Suitable for cable support system width, max.	600 mm
Suitable for cable support system width, min.	100 mm
Suitable for cable tray system height	110 mm
Adjustable connector, horizontal	no
Articulated connector, vertical	no
ROHS-conformant	yes
Rustproof steel, pickled	no
Connection type	Screw connector
Wide-span version	no