


Technical data sheet

Cable tray RKS 35 FT

Item number: 6047412



RKS 35 = Rational cable tray system with 35 mm side height.
Cable tray with continuous bottom and side perforation as well as central holes (Ø11 mm) in the base for additional fastenings.
Matching cover with turn buckle: Type AZDMD 50
Additional fastening material not included.



St	Steel
FT	Hot-dip galvanised

Master data

Item number	6047412
Type	RKS 305 FT
Description 1	Cable tray RKS
Description 2	perforated
Manufacturer	OBO
Dimension	35x50x3000
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	3
Unit of quantity	Metre
Weight	79.334 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	1,9353 kg CO2e / 1 Meter


Technical data sheet

Cable tray RKS 35 FT

Item number: 6047412



Dimensions



Dimension	35x50
Length	3,000 mm
Width	50 mm
Height	35 mm
Plate thickness	0.75 mm
Dimension L	3,000 mm

Technical data

Connector version	Without connectors
Mounting system fastening type	Floor Ceiling Wall
Walkable	no
Base perforation	7 x 32
Maintain electrical functions	no
With cover	no
Mounting perforation in base	yes
NATO hole pattern	no
Usable cross-section	16 cm ²
Usable cross-section	1600 mm ²
ROHS-conformant	yes
Rustproof steel, pickled	no
Side perforation	yes
Wide-span version	no
Load test type according to IEC 61537	Type II
Type of connector, cable support system	Screwed

Technical data sheet

Cable tray RKS 35 FT

Item number: 6047412



Loads

Insertable support spacings, min.	1 m
Insertable support spacings, max.	3 m
Support spacing 1.0 m	1.2 kN/m
Support spacing 1.5 m	0.5 kN/m
Support spacing 2.0 m	0.3 kN/m
Support spacing 2.5 m	0.1 kN/m
Support spacing 3.0 m	0.05 kN/m

