

Technical data sheet

Chequer plate cover DBKR FS

Item number: 6049123



Chequer plate cover for the walkable cable tray system, type BKR.

The cover thickness is comprised of 2.0 mm strip-galvanised sheet steel and a 1.3 mm chequer height.

Pre-marked break-out openings at a spacing of 100 mm allow retroinstallation of a turn buckle.

The covers are tested according to DIN 51130 and possess anti-slip class R11 and displacement space class V10.

Cover fastenings are not part of the scope of delivery and can be ordered separately.



St	Steel
FS	Strip galvanised

Master data

Item number	6049123
Type	DBKR 300 FS
Description 1	Chequer plate cover
Description 2	for walkable cable trays
Manufacturer	OBO
Dimension	300x3000
Colour	zinc
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	3
Unit of quantity	Metre
Weight	509.07 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	11,4497 kg CO2e / 1 Meter


Technical data sheet

Chequer plate cover DBKR FS

Item number: 6049123



Dimensions



Length	3,000 mm
Width	300 mm
Height	13 mm
Plate thickness	3.3 mm
Dimension B	300 mm
Dimension b	50 mm
Dimension L	3,000 mm

Technical data

Number of turn buckles	0 St.
Fastening type	On top
Maintain electrical functions	no
Suitable for mesh cable tray	no
Suitable for cable ladder	no
Suitable for cable tray	yes
ROHS-conformant	yes
Rustproof steel, pickled	no