

Technical data sheet

Chequer plate cover DBKR DD

Item number: 6049141



Chequer plate cover for the walkable cable tray system, type BKR.

The cover thickness is comprised of 2.0 mm of double strip-galvanised sheet steel and a 1.3 mm chequer height.

Pre-marked break-out openings at a spacing of 100 mm allow retroinstallation of a turn buckle.

When using covers outdoors, additional measures against the influence of wind must be taken.



St

Steel

DD

Strip galvanised zinc/aluminium, Double Dip

Master data

Item number	6049141
Type	DBKR 200 DD
Description 1	Corrugated steel cover
Description 2	for walkable cable trays
Manufacturer	OBO
Dimension	200x3000
Colour	zinc
Material	Steel
Surface	Strip galvanised zinc/aluminium, Double Dip
Surface standard	DIN EN 10346
Smallest sales unit	3
Unit of quantity	Metre
Weight	352.066 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	10,3938 kg CO2e / 1 Meter


Technical data sheet

Chequer plate cover DBKR DD

Item number: 6049141



Dimensions



Length	3,000 mm
Width	200 mm
Height	13 mm
Plate thickness	3.3 mm
Dimension B	200 mm
Dimension b	50 mm
Dimension L	3,000 mm

Technical data

Number of turn buckles	0 St.
Fastening type	On top
Maintain electrical functions	no
Suitable for mesh cable tray	no
Suitable for cable ladder	no
Suitable for cable tray	yes
ROHS-conformant	yes
Rustproof steel, pickled	no
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C