

Technical data sheet

Cover for stand-off mounting FT

Item number: 6051222



Cover for stand-off mounting. Not suitable for the vertical ladders SLM and SLS.

Spacers must be ordered separately for every 3 m under article number 6065475 for cable trays and cable ladders as well as under article number 6065477 for wide span systems.

When using covers outdoors, additional measures against the influence of wind must be taken.



St

Steel

FT

Hot-dip galvanised

Master data

Item number	6051222
Type	DRL FAM 230 FT
Description 1	Cover for offset mounting
Description 2	without spacer bracket
Manufacturer	OBO
Dimension	230x3000
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	3
Unit of quantity	Metre
Weight	319.24 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	6,6241 kg CO2e / 1 Meter


Technical data sheet

Cover for stand-off mounting FT

Item number: 6051222



Dimensions



Length	3,000 mm
Width	230 mm
Plate thickness	1.5 mm

Technical data

Maintain electrical functions	no
Suitable for mesh cable tray	no
Suitable for cable ladder	yes
Suitable for cable tray	yes
ROHS-conformant	yes
Rustproof steel, pickled	no