

Technical data sheet

Cover with turn buckle FT

Item number: 6051340



Cover for cable trays and cable ladders with three pairs of turn buckles.
Transverse bead from 500 mm width.
When using covers outdoors, additional measures against the influence of wind must be taken.



St	Steel
FT	Hot-dip galvanised

Master data

Item number	6051340
Type	DRL 100 FT
Description 1	Cover with turn buckle
Description 2	for cable tray and ladder
Manufacturer	OBO
Dimension	100x3000
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	3
Unit of quantity	Metre
Weight	106.67 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	2,5117 kg CO2e / 1 Meter


Technical data sheet

Cover with turn buckle FT

Item number: 6051340



Dimensions



Length	3,000 mm
Width	100 mm
Width	4 in
Height	13 mm
Plate thickness	0.03 in
Plate thickness	1 mm
Dimension B	100 mm

Technical data

Number of turn buckles	6 St.
Fastening type	Sash lock
Maintain electrical functions	no
Suitable for mesh cable tray	no
Suitable for cable ladder	yes
Suitable for cable tray	yes
ROHS-conformant	yes
Rustproof steel, pickled	no