

Technical data sheet

Cover with turn buckle A2

Item number: 6052894



Cover for cable trays and cable ladders with three pairs of turn buckles.

Transverse bead from 500 mm width.

When using covers outdoors, additional measures against the influence of wind must be taken.



A2 Stainless steel

2B Bright, treated

Master data

Item number	6052894
Type	DRL 200 A2
Description 1	Cover with turn buckle
Description 2	for cable tray and ladder
Manufacturer	OBO
Dimension	200x3000
Colour	stainless steel
Material	Stainless steel 1.4301
Surface	Bright, treated
Surface standard	
Smallest sales unit	3
Unit of quantity	Metre
Weight	183.5 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	8,9933 kg CO2e / 1 Meter


Technical data sheet

Cover with turn buckle A2

Item number: 6052894



Dimensions



Length	3,000 mm
Width	200 mm
Height	35 mm
Plate thickness	1 mm
Dimension B	200 mm
Dimension H	15 mm

Technical data

Number of turn buckles	6 St.
Fastening type	Sash lock
Maintain electrical functions	no
Suitable for mesh cable tray	no
Suitable for cable ladder	yes
Suitable for cable tray	yes
ROHS-conformant	yes
Rustproof steel, pickled	no