


Technical data sheet

Cable tray SKS 110 FS

Item number: 6061560



SKS 110 = heavy-duty cable tray system with 110 mm side height.
Magnetic shield insulation without cover 20 dB, with cover 50 dB.



St	Steel
FS	Strip galvanised

Master data

Item number	6061560
Type	SKS 160 FS
Description 1	Cable tray SKS
Description 2	perforated
Manufacturer	OBO
Dimension	110x600x3000
Colour	zinc
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	3
Unit of quantity	Metre
Weight	855.9 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	22,2594 kg CO2e / 1 Meter


Technical data sheet

Cable tray SKS 110 FS

Item number: 6061560



Dimensions



Dimension	110 x 600
Length	3,000 mm
Length	10 ft
Width	600 mm
Height	110 mm
Height	4 in
Plate thickness	0.06 in
Plate thickness	1.5 mm
Dimension W	600 mm

Technical data

Connector version	Without connectors
Mounting system fastening type	Floor Ceiling Wall
Maintain electrical functions	no
With cover	no
Mounting perforation in base	yes
NATO hole pattern	no
Usable cross-section	655 cm ²
Usable cross-section	65500 mm ²
Rustproof steel, pickled	no
Side perforation	yes
Wide-span version	no
Usable length	3000 mm
Type of connector, cable support system	Screwed

Loads

Insertable support spacings, min.	1.5 m
Insertable support spacings, max.	4 m
Support spacing 1.5 m	3 kN/m
Support spacing 2.0 m	2.4 kN/m
Support spacing 2.5 m	1.76 kN/m
Support spacing 3.0 m	1.2 kN/m
Support spacing 3.5 m	0.84 kN/m
Support spacing 4.0 m	0.8 kN/m