

Technical data sheet

Separating retainer 60 A2

Item number: 6062084



Separating retainer for the separation of cables of different voltages or functions.



A2 Stainless steel

2B Bright, treated

Master data

Item number	6062084
Type	TSG 60 A2
Description 1	Barrier strip
Description 2	for cable support systems
Manufacturer	OBO
Dimension	60x2995
Colour	stainless steel
Material	Stainless steel 1.4301
Surface	Bright, treated
Surface standard	
Smallest sales unit	3
Unit of quantity	Metre
Weight	59.265 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	2.8887 kg CO2e / 1 Meter


Technical data sheet

Separating retainer 60 A2


Item number: 6062084



Dimensions



Length	3,000 mm
Length	10 ft
Height	60 mm
Height	2 in
Plate thickness	0.75 mm
Dimension H (Inch)	2 in
Dimension H	60 mm
Dimension L	10 ft
Dimension L	3,000 mm



Technical data

Version for	L profile
Fastening type	Screw-on
Fastening perforation (ETIM)	no
Maintain electrical functions	no
Suitable for mesh cable tray	yes
Suitable for cable ladder	yes
Suitable for cable tray	yes
ROHS-conformant	yes
Rustproof steel, pickled	no