

Technical data sheet

Magic straight connector set FS

Item number: 6068900



Cable tray connector with quick fastening for the screwless connection of perforated cable trays with a side height of 35 mm. The optimised design means that the connector can be used to create radii and as a length compensation piece for large temperature deviations.



St	Steel
FS	Strip galvanised

Master data

Item number	6068900
Type	KTSMV 310 FS
Description 1	Straight connector set
Description 2	for cable tray Magic
Manufacturer	OBO
Dimension	35x100x200
Colour	zinc
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	22.7 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,8432 kg CO2e / 1 Piece


Technical data sheet

Magic straight connector set FS

Item number: 6068900



Dimensions



Dimension	35x100
Length	200 mm
Width	100 mm
Width	4 in
Height	35 mm
Height	1 in
Plate thickness	1 mm
Dimension B	100 mm

Technical data

Version for	Straight connector
Maintain electrical functions	no
Suitable for mesh cable tray	no
Suitable for cable ladder	no
Suitable for cable tray	yes
Suitable for cable tray system height	35 mm
Adjustable connector, horizontal	no
Articulated connector, vertical	no
ROHS-conformant	yes
Rustproof steel, pickled	no
Connection type	Screwless connector