


Technical data sheet

Cable tray MFR 200 FT

Item number: 6083064



MFR = mobile radio tray
Magnetic shield insulation without cover 20 dB, with cover 50 dB.



St	Steel
FT	Hot-dip galvanised

Master data

Item number	6083064
Type	MFR 240 FT
Description 1	Mobile radio channel
Description 2	perforated
Manufacturer	OBO
Dimension	200x400x3000
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	3
Unit of quantity	Metre
Weight	930.066 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	21,0875 kg CO2e / 1 Meter


Technical data sheet

Cable tray MFR 200 FT

Item number: 6083064



Dimensions



Dimension	200 x 400
Length	3,000 mm
Length	118 ft
Width	400 mm
Width	16 in
Height	200 mm
Plate thickness	0.06 in
Plate thickness	1.5 mm
Dimension B	400 mm

Technical data

Connector version	Without connectors
Mounting system fastening type	Floor Ceiling Wall
Walkable	no
Maintain electrical functions	no
With cover	no
Mounting perforation in base	yes
NATO hole pattern	no
Usable cross-section	800 cm ²
Usable cross-section	80000 mm ²
ROHS-conformant	yes
Rustproof steel, pickled	no
Side perforation	yes
Wide-span version	no
Type of connector, cable support system	Screwed