


Technical data sheet

Cover with turn buckle 200 FT

Item number: 6083150



Cover for mobile radio tray with five pairs of turn buckles.
When using covers outdoors, additional measures against the influence of wind must be taken.



St	Steel
FT	Hot-dip galvanised

Master data

Item number	6083150
Type	DMFR 200 FT
Description 1	Cover with turn buckle
Description 2	for MFR cable tray
Manufacturer	OBO
Dimension	200x3000
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	3
Unit of quantity	Metre
Weight	194.47 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	4,6422 kg CO2e / 1 Meter


Technical data sheet

Cover with turn buckle 200 FT

Item number: 6083150



Dimensions



Length	3,000 mm
Width	200 mm
Width	8 in
Height	15 mm
Plate thickness	0.06 in
Plate thickness	1 mm
Dimension B	200 mm
Dimension H	15 mm
Dimension L	3,000 mm

Technical data

Number of turn buckles	10 St.
Fastening type	Sash lock
Maintain electrical functions	no
Suitable for mesh cable tray	no
Suitable for cable ladder	yes
Suitable for cable tray	yes
ROHS-conformant	yes
Rustproof steel, pickled	no