


Technical data sheet

Straight connector wide span system FT

Item number: 6091180



Longitudinal connector for the connection of wide span cable trays and ladders of type WKSG and WKLG with a side height of 110 mm. Including appropriate bolts and combination nuts.
Including appropriate bolts, washers and nuts.



St

Steel

FT

Hot-dip galvanised

Master data

Item number	6091180
Type	WRVL 110 FT
Description 1	Straight connector
Description 2	for wide span system 110
Manufacturer	OBO
Dimension	110x500
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	2
Unit of quantity	Piece
Weight	149.5 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	3,4473 kg CO2e / 1 Piece


Technical data sheet

Straight connector wide span system FT

Item number: 6091180



Dimensions



Length	500 mm
Width	20 mm
Height	110 mm
Plate thickness	2.5 mm

Technical data

Version for	Straight connector
Maintain electrical functions	no
Suitable for mesh cable tray	no
Suitable for cable ladder	yes
Suitable for cable tray	yes
Suitable for cable tray system height	110 mm
Adjustable connector, horizontal	no
Articulated connector, vertical	no
ROHS-conformant	yes
Rustproof steel, pickled	no
Connection type	Screw connector