


Technical data sheet

D-Sub9 connection, 1 module, straight outlet, as screw connection

Item number: 6104640



Multimedia support with one D-Sub9 connection socket, straight cable outlet, with labelling panel, D-Sub9 socket (RS232) with screw connection. Support plate with locking fastening, suitable for horizontal and vertical installation in the system environment.

PC Polycarbonate

Master data		
Item number	6104640	
Type	MTG-DB9 S AL1	
Description 1	Multimedia support, D-Sub9	
Description 2	socket with screw connection	
Manufacturer	OBO	
Dimension	45x45mm	
Colour	Aluminium painted	
Material	Polycarbonate	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	2.4 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	0,0693 kg CO2e / 1 Piece	

Technical data sheet

D-Sub9 connection, 1 module, straight outlet, as screw connection


Item number: 6104640



Dimensions



Width	45 mm
Height	45 mm



Technical data

Surface version	Matt
Fastening type	Lock
Labelling panel	With labelling panel
Halogen-free	yes
Hinged cover	no
Lamp-wire connector	no
With printed label	no
With dust protection	no
ROHS-conformant	yes
Protection rating	IP20
Depth	9 mm
Support ring	no
Transparent	no
Use	D-Sub miniature
Strain relief option	no
Combination	Basic element with central cover plate