

Technical data sheet

USB 2.0/3.0 connection, 1 module, straight outlet, with connection cable
Item number: 6104925



Multimedia support with one USB 3.0 connection socket, straight cable outlet, with labelling panel, short USB 3.0 type A connection cable, socket-socket version. Support plate with locking fastening, suitable for horizontal and vertical installation in the system environment.



PC Polycarbonate

Master data		
Item number	6104925	
Type	MTG-U3A F SWGR1	
Description 1	Multimedia support,USB 3.0 A-A	
Description 2	with cable, socket-socket	
Manufacturer	OBO	
Dimension	45x45mm	
Colour	Black-grey; RAL 7021	
Material	Polycarbonate	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	6 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	0,3394 kg CO2e / 1 Piece	


Technical data sheet

USB 2.0/3.0 connection, 1 module, straight outlet, with connection cable

Item number: 6104925



Dimensions



Width	45 mm
Height	45 mm

Technical data

Surface version	Matt
Fastening type	Lock
Labelling panel	With labelling panel
Halogen-free	yes
Hinged cover	no
Lamp-wire connector	no
With printed label	yes
With dust protection	no
ROHS-conformant	yes
Protection rating	IP20
Depth	9 mm
Support ring	no
Transparent	no
Use	USB
Strain relief option	no
Combination	Basic element with central cover plate
Outlet direction	Straight