

Technical data sheet

BNC connection, 1 module, slanting outlet, as 1:1 coupling,
pure white

Item number: 6105030



Multimedia support with one BNC connection socket, slanting cable outlet, with labelling panel, BNC coupling, socket-socket version. Support plate with locking fastening, suitable for horizontal and vertical installation in the system environment.

PC Polycarbonate

Master data

Item number	6105030
Type	MTS-BC F RW1
Description 1	Multimedia support, video BNC
Description 2	1x coupling, socket-socket
Manufacturer	OBO
Dimension	45x45mm
Colour	Pure white; RAL 9010
Material	Polycarbonate
Smallest sales unit	1
Unit of quantity	Piece
Weight	1.7 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,1397 kg CO2e / 1 Piece


Technical data sheet

BNC connection, 1 module, slanting outlet, as 1:1 coupling,
pure white

Item number: 6105030



Dimensions



Width	45 mm
Height	45 mm

Technical data

Number of units	1
Surface version	Matt
Fastening type	Lock
Halogen-free	yes
Hinged cover	no
Lamp-wire connector	no
With printed label	no
With dust protection	no
ROHS-conformant	Exempt
Protection rating	IP20
Depth	26 mm
Support ring	no
Transparent	no
Use	BNC/TNC
Strain relief option	no
Combination	Basic element with central cover plate