

# Technical data sheet

Audio cinch connection, 1 module, straight outlet, as 1:1 coupling, black-grey  
Item number: 6105069



Multimedia support with two cinch connection sockets for audio R/L, straight cable outlet, with labelling panel, two cinch couplings (RCA), socket-socket version, colour coding red/white. Support plate with locking fastening, suitable for horizontal and vertical installation in the system environment.

PC Polycarbonate



| Master data                        |                                |  |
|------------------------------------|--------------------------------|--|
| Item number                        | 6105069                        |  |
| Type                               | MTG-2R F SWGR1                 |  |
| Description 1                      | Multimedia support audio cinch |  |
| Description 2                      | 2x coupling, socket-socket     |  |
| Manufacturer                       | OBO                            |  |
| Dimension                          | 45x45mm                        |  |
| Colour                             | Black-grey; RAL 7021           |  |
| Material                           | Polycarbonate                  |  |
| Smallest sales unit                | 1                              |  |
| Unit of quantity                   | Piece                          |  |
| Weight                             | 2.5 kg                         |  |
| Weight unit                        | kg/100 pc.                     |  |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,2484 kg CO2e / 1 Piece       |  |

# Technical data sheet

Audio cinch connection, 1 module, straight outlet, as 1:1 coupling, black-grey  
Item number: 6105069



## Dimensions



|        |       |
|--------|-------|
| Width  | 45 mm |
| Height | 45 mm |

## Technical data

|                      |                                        |
|----------------------|----------------------------------------|
| Number of units      | 1                                      |
| Surface version      | Matt                                   |
| Fastening type       | Lock                                   |
| Halogen-free         | yes                                    |
| Hinged cover         | no                                     |
| Lamp-wire connector  | no                                     |
| With printed label   | no                                     |
| With dust protection | no                                     |
| ROHS-conformant      | yes                                    |
| Protection rating    | IP20                                   |
| Depth                | 9 mm                                   |
| Support ring         | no                                     |
| Transparent          | no                                     |
| Use                  | Cinch                                  |
| Strain relief option | no                                     |
| Combination          | Basic element with central cover plate |
| Outlet direction     | Straight                               |