

# Technical data sheet

Speakon connection, 1 module, straight outlet, 4-pin socket, as screw connection, black-grey  
Item number: 6105272



Multimedia support with one Speakon connection socket, straight cable outlet, without labelling panel, Speakon 4-pin socket with screw connection. Support plate with locking fastening, suitable for horizontal and vertical installation in the system environment.

PC Polycarbonate

## Master data


|                                    |                              |
|------------------------------------|------------------------------|
| Item number                        | 6105272                      |
| Type                               | MTG-SON S SWGR1              |
| Description 1                      | Multimedia support, Speakon  |
| Description 2                      | socket with screw connection |
| Manufacturer                       | OBO                          |
| Dimension                          | 45x45mm                      |
| Colour                             | Black-grey; RAL 7021         |
| Material                           | Polycarbonate                |
| Smallest sales unit                | 1                            |
| Unit of quantity                   | Piece                        |
| Weight                             | 2.8 kg                       |
| Weight unit                        | kg/100 pc.                   |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,1421 kg CO2e / 1 Piece     |

# Technical data sheet

Speakon connection, 1 module, straight outlet, 4-pin socket, as screw connection, black-grey  
Item number: 6105272



## Dimensions



|        |       |
|--------|-------|
| Width  | 45 mm |
| Height | 45 mm |

## Technical data

|                      |                                        |
|----------------------|----------------------------------------|
| Surface version      | Matt                                   |
| Fastening type       | Lock                                   |
| Labelling panel      | Without labelling panel                |
| Halogen-free         | no                                     |
| Hinged cover         | no                                     |
| Lamp-wire connector  | no                                     |
| With printed label   | no                                     |
| With dust protection | no                                     |
| ROHS-conformant      | Exempt                                 |
| Protection rating    | IP20                                   |
| Depth                | 9 mm                                   |
| Support ring         | yes                                    |
| Transparent          | no                                     |
| Use                  | Loudspeaker connection                 |
| Strain relief option | no                                     |
| Combination          | Basic element with central cover plate |