

Technical data sheet

Surface-mounted socket 0° with hinged cover, protective contact, single

Item number: 6109873



Protective contact extension socket 0° with hinged cover, with screwless terminals, 2-pin, 16 A, 250 V~, with connection terminals to IEC 60884-1. Protection rating: IP44.



Master data

Item number	6109873
Type	ASD-D0 SW
Description 1	Socket single, 0°
Description 2	prot. contact w. hinged cov.
Manufacturer	OBO
Dimension	50x61mm
Colour	Black
Smallest sales unit	1
Unit of quantity	Piece
Weight	4.804 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,042 kg CO2e / 1 Piece


Technical data sheet

Surface-mounted socket 0° with hinged cover, protective contact, single

Item number: 6109873



Dimensions



Length	50 mm
Width	50 mm
Height	39 mm

Technical data

Closable	no
Connection type	Screwless terminal
Number of units	1
Number of modules (for modular construction)	1
Number of switchable sockets	0
Number of poles	2
Version for	SCHUKO
Ejection mechanism	no
Fastening type	Fastening with bolt
Labelling panel	no
Error current protection	no
Flange dimension	50x50
For more difficult conditions (according to VDE)	no
Halogen-free	no
Hinged cover	yes
Warning light	no
With on/off switch	no
With fine-wire fuse	no
With functional lighting	no
With orientation lighting	no
Mounting type	Installation
Nominal voltage	250 V
Nominal current	16 A
ROHS-conformant	Exempt
Protection rating	IP44
Special power supply	Without special power supply
Direction of insertion	Straight
Transparent	no
Rotated central insert	no
Surge protection	no
IFTTT support	no