

Technical data sheet

Rapid 45-2 device installation trunking, trunking width 160,
trunking height 53

Item number: 6113330



Trunking base and cover with base perforation for direct wall mounting.
45 mm device systems can be clicked on directly.



PVC Polyvinylchloride

Master data

Item number	6113330
Type	GK-53160-3RW
Description 1	Device installation trunking
Description 2	Rapid 45-2, 3-compartment
Manufacturer	OBO
Dimension	2000x160x53
Colour	Pure white; RAL 9010
Material	Polyvinylchloride
Smallest sales unit	8
Unit of quantity	Metre
Weight	220 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	4,272 kg CO2e / 1 Meter


Technical data sheet

Rapid 45-2 device installation trunking, trunking width 160,
trunking height 53

Item number: 6113330



Dimensions



Length	2,000 mm
Width	160 mm
Height	53 mm

Technical data

Number of covers	3
Number of insertable partitions	3
Rear panel version (inner side)	Other continuous profile
Rectangular shape	yes
Base perforation	With base perforation
Halogen-free	no
Cable retaining clip	no
Duct connector	no
Cover mounting type	Internal
Mounting perforation in base	yes
Usable cross-section	6480 mm ²
Cover supplied	yes
Cover width	45 mm
Cover width 2	45 mm
Cover width 3	45 mm
Protective film	yes
Symmetrical	yes