


Technical data sheet

Device installation trunking Rapid 45-2, trunking width 100,
trunking height 53, halogen-free
Item number: 6114157



Wall and ceiling trunking, halogen-free, consisting of base and cover for mounting directly on the wall.
During installation, ensure that only halogen-free accessories and fastening materials are used.



Polycarbonate/Acrylnitrile-butadiene-styrene

Master data


Item number	6114157
Type	GKH-53100RW
Description 1	Device inst.trunk.halogen-free
Description 2	Rapid 45-2, 1-compartment
Manufacturer	OBO
Dimension	2000x100x53
Colour	Pure white; RAL 9010
Material	Polycarbonate/Acrylnitrile-butadiene-styrene
Smallest sales unit	2
Unit of quantity	Metre
Weight	109.7 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	5,9294 kg CO2e / 1 Meter

Technical data sheet

Device installation trunking Rapid 45-2, trunking width 100,
trunking height 53, halogen-free
Item number: 6114157



Dimensions



Length	2,000 mm
Width	100 mm
Height	53 mm

Technical data

Number of covers	1
Number of insertable partitions	1
Rear panel version (inner side)	Continuous C profile
Rectangular shape	yes
Base perforation	With base perforation
Halogen-free	yes
Cable retaining clip	no
Duct connector	no
Cover mounting type	Internal
Mounting perforation in base	yes
Usable cross-section	4400 mm ²
Cover supplied	yes
Cover width	45 mm
Cover width 2	0 mm
Cover width 3	0 mm
ROHS-conformant	yes
Protection rating	IP40
Protective film	yes
Protection rating IK code	IK08
Symmetrical	yes
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-15 °C