

Technical data sheet

Deskbox DBV, 2 sockets

Item number: 6116858



Lowerable Deskbox with connection cable for fixed installation on a tabletop, plastic fastening sleeve, painted accordingly in cover shade. It is mounted using a drill hole (Ø102 mm) in the tabletop.

Equipment:

- Two black protection contact sockets in 60° connection direction, incl. 3.0 m power cable with angular connector CEE 7/7.

Note: Can be used in table tops of up to 50 mm thickness.

The ready-for-connection type DBV Deskbox is particularly suitable for the direct supply of workstations with energy, communication and data technology connections.

Alu	Aluminium
EL	Anodised

Master data

Item number	6116858
Type	DBV-A3E D2S
Description 1	Deskbox, lowerable
Description 2	for installation in table tops
Manufacturer	OBO
Colour	aluminium
Material	Aluminium
Surface	Anodised
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	99.23 kg
Weight unit	kg/100 pc.


Technical data sheet

Deskbox DBV, 2 sockets

Item number: 6116858



Dimensions



Length	212 mm
--------	--------

Technical data

Number of audio connections	0
Number of CAT 5 connections	0
Number of CAT 5E connections	0
Number of CAT 6 connections	0
Number of USB connections	0
Number of VGA connections	0
Number of HDMI connections	0
Number of socket outlets with protective contact CEE 7/3 (type F)	2
Version for	Stainless steel lid
Version for	Installation
Extendable	yes
Shape	Round
Foldable	no
Length of the supply cable	3 m
ROHS-conformant	Exempt
Surge protection	no