

Technical data sheet

Roller blind button, 1 module

Item number: 6120980



Roller blind button with electrical locking, 1-pin, 10 A, 250 V~, with screwless terminals.



PC Polycarbonate

| Master data         |                         |  |
|---------------------|-------------------------|--|
| Item number         | 6120980                 |  |
| Type                | RT-BS RW1               |  |
| Description 1       | Roller blind pushbutton |  |
| Manufacturer        | OBO                     |  |
| Dimension           | 10 A, 250 V             |  |
| Colour              | Pure white; RAL 9010    |  |
| Material            | Polycarbonate           |  |
| Smallest sales unit | 1                       |  |
| Unit of quantity    | Piece                   |  |
| Weight              | 3.7 kg                  |  |
| Weight unit         | kg/100 pc.              |  |

| Dimensions |           |         |
|------------|-----------|---------|
|            | Dimension | 45 x 45 |
|            |           |         |

# Technical data sheet

## Roller blind button, 1 module

Item number: 6120980



### Technical data

|                                              |                          |
|----------------------------------------------|--------------------------|
| Number of modules (for modular construction) | 1                        |
| Surface version                              | Matt                     |
| Version for                                  | Switch, 1 pin            |
| Operation type                               | Rocker                   |
| Fastening type                               | Lock                     |
| Labelling panel                              | no                       |
| Halogen-free                                 | yes                      |
| Mounting type                                | Device installation duct |
| Nominal voltage                              | 250 V                    |
| Nominal current                              | 10 A                     |
| ROHS-conformant                              | yes                      |
| Protection rating                            | IP20                     |
| Transparent                                  | no                       |
| Combination                                  | Miscellaneous            |