

Technical data sheet

Cable routing trunking LE 10, trunking width 10

Item number: 6130002



LE cable routing trunking for covered cable routing in internal areas.
Trunking base with base perforation for mounting. Hardly inflammable and self-extinguishing after removal of a naked flame. Change the direction with the fittings and close the trunking ends with end pieces.
Tested to DIN EN 50085-1 and DIN EN 50085-2-1.
Base and cover in set.



PVC Polyvinylchloride

Master data

Item number	6130002
Type	WDK10010SRW
Description 1	Wall trunking system
Description 2	with adhesive film
Manufacturer	OBO
Dimension	2000x10x10
Colour	Pure white; RAL 9010
Material	Polyvinylchloride
Smallest sales unit	180
Unit of quantity	Metre
Weight	6.7 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	0,3465 kg CO2e / 1 Meter

Dimensions

Length	2,000 mm
Width	12.6 mm
Height	10 mm

Technical data sheet

Cable routing trunking LE 10, trunking width 10

Item number: 6130002



Technical data

Version, cable trunking cover	Loose
Fastening type	Self-adhesive
Halogen-free	no
Cable retaining clip	no
Duct connector	no
Delivery on a roll	no
ROHS-conformant	yes
Protection rating	IP30
Protective film	no
Protection rating IK code	IK06
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C
Transparent	no