

Technical data sheet

Cable routing trunking MKS 25, trunking width 38, with partition

Item number: 6130165



MKS mini trunking for covered cable routing in internal areas.
Trunking base with base perforation for direct mounting on the wall and partition
to install different voltage levels.
Base and cover as set.



PVC Polyvinylchloride

Master data

Item number	6130165
Type	MKS 2538 TW rws
Description 1	Cable trunking
Description 2	LE Set 25x38 Sep. 9010
Manufacturer	OBO
Dimension	2000x38x25
Colour	Pure white; RAL 9010
Material	Polyvinylchloride
Smallest sales unit	30
Unit of quantity	Metre
Weight	29 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	0,6299 kg CO2e / 1 Meter

Dimensions

Length	2,000 mm
Width	38 mm
Height	25 mm

Technical data sheet

Cable routing trunking MKS 25, trunking width 38, with partition

Item number: 6130165



Technical data

Number of fixed partitions	1
Number of cables NYM 3 x 1.5 mm ² Ø 10.5 mm (without socket)	3
Number of insertable partitions	0
Fastening type	Base perforation
Maintain electrical functions	no
Halogen-free	no
Cable retaining clip	no
Duct connector	no
Delivery on a roll	no
Usable cross-section	730 mm ²
ROHS-conformant	yes
Protective film	no
Transparent	no