

Technical data sheet

Trunking, type WDKH 10020

Item number: 6175375



Trunking cover and base with base perforation made of halogen-free plastic. During installation, ensure that only halogen-free accessories and fastening materials are used.



PC/ABS

Polycarbonate/Acrylnitrile-butadiene-styrene

| Master data                        |                                              |
|------------------------------------|----------------------------------------------|
| Item number                        | 6175375                                      |
| Type                               | WDKH-10020RW                                 |
| Description 1                      | Wall trunking system                         |
| Description 2                      | halogen-free                                 |
| Manufacturer                       | OBO                                          |
| Dimension                          | 10x20x2000                                   |
| Colour                             | Pure white; RAL 9010                         |
| Material                           | Polycarbonate/Acrylnitrile-butadiene-styrene |
| Smallest sales unit                | 96                                           |
| Unit of quantity                   | Metre                                        |
| Weight                             | 8.5 kg                                       |
| Weight unit                        | kg/100 m                                     |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,4304 kg CO2e / 1 Meter                     |


# Technical data sheet

## Trunking, type WDKH 10020



Item number: 6175375

### Dimensions



|        |          |
|--------|----------|
| Length | 2,000 mm |
| Width  | 20 mm    |
| Height | 10 mm    |

### Technical data

|                                   |                       |
|-----------------------------------|-----------------------|
| Number of fixed partitions        | 0                     |
| Number of insertable partitions   | 0                     |
| Version, cable trunking cover     | Loose                 |
| Fastening type                    | Base perforation      |
| Base perforation                  | with base perforation |
| Halogen-free                      | yes                   |
| Cable retaining clip              | no                    |
| Duct connector                    | no                    |
| Usable cross-section              | 135 mm <sup>2</sup>   |
| ROHS-conformant                   | yes                   |
| Protection rating                 | IP30                  |
| Protective film                   | no                    |
| Protection rating IK code         | IK07.                 |
| Permitted temperature range, max. | 90 °C                 |
| Permitted temperature range, min. | -5 °C                 |