

Technical data sheet

Trunking, type WDKH 15030

Item number: 6175392



Duct cover and base with base perforation made of halogen-free plastic. With self-adhesive film for fastening on the underside.
During installation, ensure that only halogen-free accessories and fastening materials are used.



Polycarbonate/Acrylnitrile-butadiene-styrene

Master data

Item number	6175392
Type	WDKH-15030RW T
Description 1	Wall trunking system
Description 2	halogen-free
Manufacturer	OBO
Dimension	15x30x2000
Colour	Pure white; RAL 9010
Material	Polycarbonate/Acrylnitrile-butadiene-styrene
Smallest sales unit	32
Unit of quantity	Metre
Weight	16 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	1,4402 kg CO2e / 1 Meter


Technical data sheet

Trunking, type WDKH 15030

Item number: 6175392



Dimensions



Length	2,000 mm
Width	30 mm
Height	17.5 mm

Technical data

Number of fixed partitions	0
Number of insertable partitions	0
Version, cable trunking cover	Loose
Fastening type	Base perforation
Base perforation	with base perforation
Halogen-free	yes
Cable retaining clip	no
Duct connector	no
Usable cross-section	375 mm ²
ROHS-conformant	yes
Protection rating	IP30
Protective film	no
Protection rating IK code	IK07.
Permitted temperature range, max.	90 °C
Permitted temperature range, min.	-5 °C