

Technical data sheet

T and intersection cover, for trunking type WDKH 60150

Item number: 6175714



T and intersection cover for changing the direction of the halogen-free WDKH trunking. The fitting is preperforated at the side for the connection of different trunking cross-sections.



Polycarbonate/Acrylnitrile-butadiene-styrene

Master data

Item number	6175714
Type	WDKH-T60150RW
Description 1	T- and crosspiece cover
Description 2	halogen-free
Manufacturer	OBO
Dimension	60x150mm
Colour	Pure white; RAL 9010
Material	Polycarbonate/Acrylnitrile-butadiene-styrene
Smallest sales unit	2
Unit of quantity	Piece
Weight	23.463 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	1,3714 kg CO2e / 1 Piece


Technical data sheet

T and intersection cover, for trunking type WDKH 60150

Item number: 6175714



Dimensions



Length	291 mm
Width	150 mm
Height	60 mm
Dimension a	291 mm
Dimension b	155 mm

Technical data

Version for	Hood fitting
Fastening type	Lockable
Maintain electrical functions	no
for duct dimension	60x
Halogen-free	yes
Trunking depth	60 mm
ROHS-conformant	yes
Protection rating	IP30
Protective film	no
Protection rating IK code	IK07.
Permitted temperature range, max.	90 °C
Permitted temperature range, min.	-5 °C