

Technical data sheet

Wiring trunking, type LK4 60025

Item number: 6178028



Wiring duct, incl. cover and base perforation, for horizontal and vertical routing of electrical cables in the switchgear cabinet. Designed as a metric duct. The nominal dimension of the system size corresponds to the internal dimension of the duct. Retainers are broken out without tools. The flush-floor routing of cables is possible through predetermined break points. Tested to DIN EN 50085-2-3. Special lengths on request.



PVC Polyvinylchloride

Master data

Item number	6178028
Type	LK4 60025
Description 1	Slotted cable trunking system
Manufacturer	OBO
Dimension	60x25x2000
Colour	Stone grey; RAL 7030
Material	Polyvinylchloride
Smallest sales unit	2
Unit of quantity	Metre
Weight	46 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	1,2247 kg CO2e / 1 Meter


Technical data sheet

Wiring trunking, type LK4 60025

Item number: 6178028



Dimensions



Length	2,000 mm
Width	25 mm
Height	60 mm

Technical data

Side wall version	Slotted
Fastening type	Base perforation
Flexible	no
Halogen-free	no
Creepage current-resistant	yes
With cover	yes
Usable cross-section	13.56 cm ²
ROHS-conformant	yes
Slot spacing	10 mm
Slot width	4 mm
Self-extinguishing	yes
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C