

Technical data sheet

Wire retainer for type LKVH

Item number: 6178650



Wire retainer for halogen-free wiring trunking, type LKVH. The wire retainer prevents already inserted cables from falling out. These predetermined breaking points allow the length to be reduced for various trunking widths to 38, 28 and 23 mm.



Polystyrene

Master data		
Item number	6178650	
Type	LKV H H	
Description 1	Wire retainer	
Description 2	for LKV/H	
Manufacturer	OBO	
Colour	Light grey; RAL 7035	
Material	Polystyrene	
Smallest sales unit	100	
Unit of quantity	Piece	
Weight	0.349 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	0,0133 kg CO2e / 1 Piece	


Technical data sheet

Wire retainer for type LKVH

Item number: 6178650



Dimensions



Width	56 mm
Height	25 mm
Dimension a	56 mm
Dimension b	25 mm

Technical data

Adjustable to duct width	yes
Halogen-free	yes
ROHS-conformant	yes
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C