

Technical data sheet

Trunking, type WDK 13025

Item number: 6187714



Trunking cover and base with base perforation. The heads of the fastening screws are hidden in the raised floor of the trunking. Assignment with cables with basic isolation is permitted. Please note the delivery lengths of 2 m and 4 m. Pure white = similar to RAL 9010, pearl white = similar to RAL 1013.



PVC Polyvinylchloride

Master data

Item number	6187714
Type	WDK13025
Description 1	Wall trunking system
Description 2	with raised floor mounting
Manufacturer	OBO
Dimension	13x25x2000
Colour	Oyster white; RAL 1013
Material	Polyvinylchloride
Smallest sales unit	24
Unit of quantity	Metre
Weight	16.4 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	0,3231 kg CO2e / 1 Meter


Technical data sheet

Trunking, type WDK 13025

Item number: 6187714



Dimensions



Length	2,000 mm
Width	25 mm
Height	13.5 mm

Technical data

Number of fixed partitions	0
Number of insertable partitions	0
Version, cable trunking cover	Loose
Fastening type	Base perforation
Maintain electrical functions	no
Halogen-free	no
Cable retaining clip	no
Duct connector	no
Delivery on a roll	no
ROHS-conformant	yes
Protection rating	IP30
Protective film	no
Protection rating IK code	IK04
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C