

# Technical data sheet

## Trunking, type WDK 80210

Item number: 6191312



Wall installation trunking as trunking base with base perforation and matching trunking cover.  
Four cover fixing devices included.  
The lid clamp can be moved along the entire length of the trunking.



**PVC** Polyvinylchloride

### Master data

|                                    |                         |
|------------------------------------|-------------------------|
| Item number                        | 6191312                 |
| Type                               | WDK80210RW              |
| Description 1                      | Wall trunking system    |
| Description 2                      | with base perforation   |
| Manufacturer                       | OBO                     |
| Dimension                          | 80x210x2000             |
| Colour                             | Pure white; RAL 9010    |
| Material                           | Polyvinylchloride       |
| Smallest sales unit                | 8                       |
| Unit of quantity                   | Metre                   |
| Weight                             | 240 kg                  |
| Weight unit                        | kg/100 m                |
| CO2 Footprint (GWP) Cradle-to-Gate | 5,565 kg CO2e / 1 Meter |


# Technical data sheet

Trunking, type WDK 80210

Item number: 6191312



## Dimensions



|        |          |
|--------|----------|
| Length | 2,000 mm |
| Width  | 210 mm   |
| Height | 80 mm    |

# Technical data sheet

Trunking, type WDK 80210

Item number: 6191312



## Technical data

|                                                                         |                       |
|-------------------------------------------------------------------------|-----------------------|
| Number of fixed partitions                                              | 0                     |
| Number of cables NYM 3 x 1.5 mm <sup>2</sup> Ø 10.5 mm (without socket) | 80                    |
| Number of cables NYM 3 x 2.5 mm <sup>2</sup> Ø 11.5 mm (without socket) | 67                    |
| Number of cables NYM 5 x 1.5 mm <sup>2</sup> Ø 12.0 mm (without socket) | 61                    |
| Number of insertable partitions                                         | 2                     |
| Version, cable trunking cover                                           | Loose                 |
| Fastening type                                                          | Base perforation      |
| Maintain electrical functions                                           | no                    |
| Halogen-free                                                            | no                    |
| Cable retaining clip                                                    | yes                   |
| Duct connector                                                          | no                    |
| Delivery on a roll                                                      | no                    |
| Usable cross-section                                                    | 13980 mm <sup>2</sup> |
| ROHS-conformant                                                         | yes                   |
| Protection rating                                                       | IP30                  |
| Protective film                                                         | no                    |
| Protection rating IK code                                               | IK04                  |
| Permitted temperature range, max.                                       | 60 °C                 |
| Permitted temperature range, min.                                       | -5 °C                 |
| Weatherproof                                                            | yes                   |