

Technical data sheet

Trunking, type WDK 100230

Item number: 6191355



Wall installation trunking as trunking base with base perforation and matching trunking cover.
Four cover fixing devices included.
Lid clamp can be moved along the entire length of the trunking.



PVC Polyvinylchloride

Master data

Item number	6191355
Type	WDK100230RW
Description 1	Wall trunking system
Description 2	with base perforation
Manufacturer	OBO
Dimension	100x230x2000
Colour	Pure white; RAL 9010
Material	Polyvinylchloride
Smallest sales unit	4
Unit of quantity	Metre
Weight	338 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	6,4628 kg CO2e / 1 Meter


Technical data sheet

Trunking, type WDK 100230

Item number: 6191355



Dimensions



Length	2,000 mm
Width	230 mm
Height	100 mm

Technical data sheet

Trunking, type WDK 100230

Item number: 6191355



Technical data

Number of fixed partitions	0
Number of cables NYM 3 x 1.5 mm² Ø 10.5 mm (without socket)	113
Number of cables NYM 3 x 2.5 mm² Ø 11.5 mm (without socket)	148
Number of cables NYM 5 x 1.5 mm² Ø 12.0 mm (without socket)	87
Number of insertable partitions	3
Version, cable trunking cover	Loose
Fastening type	Base perforation
Maintain electrical functions	no
Halogen-free	no
Cable retaining clip	yes
Duct connector	no
Delivery on a roll	no
Usable cross-section	19702 mm²
ROHS-conformant	yes
Protection rating	IP30
Protective film	no
Protection rating IK code	IK04
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C
Weatherproof	yes