


Technical data sheet

End piece, for trunking type WDK 13025

Item number: 6193088



End piece to close the WDK trunking.
The end pieces are pushed onto the trunking and kept in place by the spring action.



Polycarbonate/Acrylnitrile-butadiene-styrene

Master data

Item number	6193088
Type	WDK HE13025PW
Description 1	End piece
Manufacturer	OBO
Dimension	13x25x40
Colour	Oyster white; RAL 1013
Material	Polycarbonate/Acrylnitrile-butadiene-styrene
Smallest sales unit	10
Unit of quantity	Piece
Weight	0.385 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,0287 kg CO2e / 1 Piece


Technical data sheet

End piece, for trunking type WDK 13025


Item number: 6193088



Dimensions



Length	40 mm
Width	25 mm
Height	13.5 mm



Technical data

Version for	Left/right
Fastening type	Lockable
Halogen-free	no
ROHS-conformant	yes
Protection rating	IP30
Protective film	no
Protection rating IK code	IK04
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C