

# Technical data sheet

## Cross-over 110 FS

Item number: 6219682



Cross-over for the creation of horizontal branches, fitting for cable ladders of side height 110 mm. With connector perforation. Can be used in indoor areas. Connector and fastening material must be ordered separately. Fittings must be supported by the support structure.



St

Steel

FS

Strip galvanised

### Master data

|                                    |                              |
|------------------------------------|------------------------------|
| Item number                        | 6219682                      |
| Type                               | LK 1120 R5 FS                |
| Description 1                      | Cross over                   |
| Description 2                      | for cable ladder, horizontal |
| Manufacturer                       | OBO                          |
| Dimension                          | 110x200                      |
| Colour                             | zinc                         |
| Material                           | Steel                        |
| Surface                            | Strip galvanised             |
| Surface standard                   | DIN EN 10346                 |
| Smallest sales unit                | 1                            |
| Unit of quantity                   | Piece                        |
| Weight                             | 1261 kg                      |
| Weight unit                        | kg/100 pc.                   |
| CO2 Footprint (GWP) Cradle-to-Gate | 35,6833 kg CO2e / 1 Piece    |


# Technical data sheet

## Cross-over 110 FS

Item number: 6219682



### Dimensions



|             |        |
|-------------|--------|
| Width       | 200 mm |
| Height      | 110 mm |
| Dimension B | 200 mm |
| Dimension R | 500 mm |

### Technical data

|                               |                      |
|-------------------------------|----------------------|
| Version of the rungs          | Profile unperforated |
| Side rail version             | Profile (open)       |
| Maintain electrical functions | no                   |
| ROHS-conformant               | yes                  |
| Rustproof steel, pickled      | no                   |
| Wide-span version             | no                   |
| Rail thickness                | 1.5 mm               |