


Technical data sheet

Rung support plate for the maintenance of electrical function FT

Item number: 6223044



Rung support plates to increase the support surface for the cables in the fittings for routing types with cable ladders for the maintenance of electrical function to DIN 4102 Part 12. Use the rung support plates to ensure the largest possible support surface in the cable ladder fittings for the function maintenance cables in case of fire. The rung support plates are just laid loosely on the rungs of the cable ladder fittings. The lugs pointing down prevent slippage. For cable ladder width 400 mm.



St	Steel
FT	Hot-dip galvanised

Master data

Item number	6223044
Type	SAB40 FT
Description 1	Rung support plate
Description 2	for function maintenance
Manufacturer	OBO
Dimension	380x140x16,5
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	25
Unit of quantity	Piece
Weight	71 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	1,9126 kg CO2e / 1 Piece


Technical data sheet

Rung support plate for the maintenance of electrical function FT

Item number: 6223044



Dimensions



Height	16.5 mm
Dimension a	60 mm
Dimension B	380 mm
Dimension b	75 mm

Technical data

Material thickness	1.5 mm
ROHS-conformant	yes