

Technical data sheet

90° bend 60 A4

Item number: 6225102



90° bend, horizontal, with welded rung for all cable ladder types of 60 mm side height.
Connectors should be ordered separately and in the appropriate quantity.



A4	Stainless steel
2B	Bright, treated

Master data

Item number	6225102
Type	LB 90 620 R3 A4
Description 1	90° bend
Description 2	for cable ladder
Manufacturer	OBO
Dimension	60x200
Colour	stainless steel
Material	Stainless steel 1.4571
Surface	Bright, treated
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	261 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	13,6761 kg CO2e / 1 Piece


Technical data sheet

90° bend 60 A4

Item number: 6225102



Dimensions



Width	200 mm
Height	60 mm
Dimension B	200 mm
Dimension R	200 mm

Technical data

Bend (angle)	90°
Version of the rungs	Profile perforated
Side rail version	Flat profile
Connector version	Without connectors
Maintain electrical functions	no
Change of direction	Horizontal
ROHS-conformant	yes
Rustproof steel, pickled	no
Hinged	no
Side perforation	no
Wide-span version	no
Rail thickness	1.5 mm