


Technical data sheet

DD cover with turn buckle

Item number: 6227604



Cover with turn buckles for wide span cable trays and wide span cable ladders with side heights of 110 and 160 mm.
Transverse bead from 500 mm width.
Take appropriate constructive protection measures if there are high wind speeds.



St Steel

DD Strip galvanised zinc/aluminium, Double Dip

Master data

Item number	6227604
Type	WDRL 111630 DD
Description 1	Cover with turn buckle
Description 2	wide span system 110 and 160
Manufacturer	OBO
Dimension	300x3000
Colour	zinc
Material	Steel
Surface	Strip galvanised zinc/aluminium, Double Dip
Surface standard	DIN EN 10346
Smallest sales unit	3
Unit of quantity	Metre
Weight	263.34 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	6,0875 kg CO2e / 1 Meter


Technical data sheet

DD cover with turn buckle

Item number: 6227604



Dimensions



Length	3,000 mm
Width	300 mm
Height	110 mm
Plate thickness	1 mm
Dimension B	300 mm
Dimension H	15 mm
Dimension L	3,000 mm

Technical data

Number of turn buckles	6 St.
Fastening type	Sash lock
Maintain electrical functions	no
Suitable for mesh cable tray	no
Suitable for cable ladder	yes
Suitable for cable tray	yes
ROHS-conformant	yes
Rustproof steel, pickled	no