


# Technical data sheet

## DD cover with turn buckle

Item number: 6227612



Cover with turn buckles for wide span cable trays and wide span cable ladders with side heights of 110 and 160 mm.  
Transverse bead from 500 mm width.  
Take appropriate constructive protection measures if there are high wind speeds.



**St** Steel

**DD** Strip galvanised zinc/aluminium, Double Dip

### Master data

|                                    |                                             |
|------------------------------------|---------------------------------------------|
| Item number                        | 6227612                                     |
| Type                               | WDRL 1116 50 DD                             |
| Description 1                      | Cover with turn buckle                      |
| Description 2                      | wide span system 110 and 160                |
| Manufacturer                       | OBO                                         |
| Dimension                          | 500x3000                                    |
| Colour                             | zinc                                        |
| Material                           | Steel                                       |
| Surface                            | Strip galvanised zinc/aluminium, Double Dip |
| Surface standard                   | DIN EN 10346                                |
| Smallest sales unit                | 3                                           |
| Unit of quantity                   | Metre                                       |
| Weight                             | 626.67 kg                                   |
| Weight unit                        | kg/100 m                                    |
| CO2 Footprint (GWP) Cradle-to-Gate | 14,273 kg CO2e / 1 Meter                    |


# Technical data sheet

## DD cover with turn buckle

Item number: 6227612



### Dimensions



|                 |          |
|-----------------|----------|
| Length          | 3,000 mm |
| Width           | 500 mm   |
| Height          | 110 mm   |
| Plate thickness | 1.5 mm   |
| Dimension B     | 500 mm   |
| Dimension H     | 15 mm    |
| Dimension L     | 3,000 mm |

### Technical data

|                               |           |
|-------------------------------|-----------|
| Number of turn buckles        | 6 St.     |
| Fastening type                | Sash lock |
| Maintain electrical functions | no        |
| Suitable for mesh cable tray  | no        |
| Suitable for cable ladder     | yes       |
| Suitable for cable tray       | yes       |
| ROHS-conformant               | yes       |
| Rustproof steel, pickled      | no        |