

Technical data sheet

Cover incl. turn buckles DD

Item number: 6232402



Cover for wide span ladders with the side height of 200 mm.
Transverse bead from 500 mm width.
Take appropriate constructive protection measures if there are high wind speeds.



St Steel

DD Strip galvanised zinc/aluminium, Double Dip

Master data

Item number	6232402
Type	WKLD 2020 DD
Description 1	Cover with turn buckle
Description 2	wide span system 200
Manufacturer	OBO
Dimension	200x3000
Colour	zinc
Material	Steel
Surface	Strip galvanised zinc/aluminium, Double Dip
Surface standard	DIN EN 10346
Smallest sales unit	3
Unit of quantity	Metre
Weight	188 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	4,2224 kg CO2e / 1 Meter


Technical data sheet

Cover incl. turn buckles DD

Item number: 6232402



Dimensions



Length	3,000 mm
Width	200 mm
Height	200 mm
Plate thickness	1.5 mm
Dimension B	200 mm
Dimension H	15 mm
Dimension L	3,000 mm

Technical data

Fastening type	Sash lock
Maintain electrical functions	no
Suitable for mesh cable tray	no
Suitable for cable ladder	yes
Suitable for cable tray	yes
ROHS-conformant	yes
Rustproof steel, pickled	no