


Technical data sheet

Foot plate for wide-span systems

Item number: 6232510



Foot plate to accept wide-span systems, e.g. for vertical routing of wide-span cable trays. Including screws, washers and nuts.



St

Steel

FT

Hot-dip galvanised

Master data

Item number	6232510
Type	WFP 160 FT
Description 1	Base plate
Description 2	for wide span system 160
Manufacturer	OBO
Dimension	160
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	1
Unit of quantity	Piece
Weight	333 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	8,7126 kg CO2e / 1 Piece


Technical data sheet

Foot plate for wide-span systems



Item number: 6232510

Dimensions



Length	382 mm
Width	169 mm
Height	20 mm

Technical data

Version for	Screw head plate
Maintain electrical functions	no
Suitable for ceiling fastening	no
Suitable for panel fastening	no
Suitable for profile shapes	C profile
ROHS-conformant	yes
Rustproof steel, pickled	no
Angle range, max.	90 mm
Angle range, min.	90 mm