

Technical data sheet

Cable trunking, type LKM 80080

Item number: 6247194



Trunking cover and base with base perforation.
Equipotential bonding is guaranteed between the cover and the base without any additional aids.



St	Steel
FS	Strip galvanised

Master data

Item number	6247194
Type	LKM80080FS
Description 1	Cable trunking
Description 2	with base perforation
Manufacturer	OBO
Dimension	80x80x2000
Colour	zinc
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	2
Unit of quantity	Metre
Weight	214.8 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	6,1191 kg CO2e / 1 Meter


Technical data sheet

Cable trunking, type LKM 80080

Item number: 6247194



Dimensions



Length	2,000 mm
Width	80 mm
Height	80 mm

Technical data

Number of fixed partitions	0
Number of cables NYM 3 x 1.5 mm² Ø 10.5 mm (without socket)	42
Number of cables NYM 3 x 2.5 mm² Ø 11.5 mm (without socket)	30
Number of cables NYM 5 x 1.5 mm² Ø 12.0 mm (without socket)	30
Number of insertable partitions	1
Version, cable trunking cover	Loose
Fastening type	Base perforation
Base perforation	with base perforation
Maintain electrical functions	no
Halogen-free	yes
Cable retaining clip	no
Duct connector	no
Delivery on a roll	no
Usable cross-section	6075 mm²
ROHS-conformant	yes
Protection rating	IP30
Protective film	no
Protection rating IK code	IK10
Permitted temperature range, max.	90 °C
Permitted temperature range, min.	-5 °C
Transparent	no