

Technical data sheet

Flat angle, for cable duct type LKM 60100

Item number: 6248004



Flat angle including cover for changing the direction of the LKM ducts.
Equipotential bonding without additional aids, between base and cover



St	Steel
FS	Strip galvanised

Master data

Item number	6248004
Type	LKM F60100FS
Description 1	Flat angle
Description 2	with cover
Manufacturer	OBO
Dimension	60x100mm
Colour	zinc
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	63.4 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	3,2241 kg CO2e / 1 Piece


Technical data sheet

Flat angle, for cable duct type LKM 60100

Item number: 6248004



Dimensions



Length	240 mm
Width	100 mm
Height	64 mm
Dimension a	120 mm

Technical data

Version for	Base and cover
Fastening type	Base perforation
Maintain electrical functions	yes
for duct dimension	60 x 100
Halogen-free	yes
Duct height, min.	64 mm
Trunking depth	64 mm
ROHS-conformant	yes
Protection rating	IP30
Protective film	no
Protection rating IK code	IK10
Self-extinguishing	no
Permitted temperature range, max.	90 °C
Permitted temperature range, min.	-5 °C
Angle range, max.	90 mm
Angle range, min.	90 mm