


# Technical data sheet

## T piece for cable duct type LKM 60100

Item number: 6248209



T piece including cover for changing the direction of the LKM ducts.  
Equipotential bonding without additional aids, between base and cover



|    |                  |
|----|------------------|
| St | Steel            |
| FS | Strip galvanised |

### Master data

|                                    |                         |
|------------------------------------|-------------------------|
| Item number                        | 6248209                 |
| Type                               | LKM T60100FS            |
| Description 1                      | T piece                 |
| Description 2                      | with cover              |
| Manufacturer                       | OBO                     |
| Dimension                          | 60x100mm                |
| Colour                             | zinc                    |
| Material                           | Steel                   |
| Surface                            | Strip galvanised        |
| Surface standard                   | DIN EN 10346            |
| Smallest sales unit                | 1                       |
| Unit of quantity                   | Piece                   |
| Weight                             | 69.2 kg                 |
| Weight unit                        | kg/100 pc.              |
| CO2 Footprint (GWP) Cradle-to-Gate | 2,652 kg CO2e / 1 Piece |

# Technical data sheet


## T piece for cable duct type LKM 60100

Item number: 6248209



### Dimensions

|             |        |
|-------------|--------|
| Length      | 300 mm |
| Width       | 100 mm |
| Height      | 64 mm  |
| Dimension a | 300 mm |



### Technical data

|                                   |                  |
|-----------------------------------|------------------|
| Departing width                   | 100 mm           |
| Departing height                  | 64 mm            |
| Version for                       | Base and cover   |
| Fastening type                    | Base perforation |
| Maintain electrical functions     | yes              |
| for duct dimension                | 60 x 100         |
| Halogen-free                      | yes              |
| Duct height, min.                 | 64 mm            |
| Trunking depth                    | 64 mm            |
| ROHS-conformant                   | yes              |
| Protection rating                 | IP30             |
| Protective film                   | no               |
| Protection rating IK code         | IK10             |
| Permitted temperature range, max. | 90 °C            |
| Permitted temperature range, min. | -5 °C            |