


Technical data sheet

Device installation trunking, desk trunking

Item number: 6282700



GEK-S device installation trunking suitable for installation on desks, etc. The visible surfaces of the painted GEK-S device installation trunking are laminated. The trunking system possesses self-contacting locking straps to accept a sheet steel partition. The equipotential bonding between the trunking bases takes place using the coupling. The protective measure and the equipotential bonding is guaranteed between the cover and the base by the self-contacting trunking cover. The actual system opening is 76.5 mm. The cover must be ordered separately.



St Steel

Master data

Item number	6282700
Type	GEK-SA133110RW
Description 1	Device installation trunking
Description 2	asymmetrical
Manufacturer	OBO
Dimension	133x110x2000
Colour	Pure white; RAL 9010
Material	Steel
Smallest sales unit	2
Unit of quantity	Metre
Weight	332 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	7,6511 kg CO2e / 1 Meter


Technical data sheet

Device installation trunking, desk trunking

Item number: 6282700



Dimensions



Length	2,000 mm
Width	110 mm
Height	133 mm

Technical data

Number of covers	1
Number of insertable partitions	1
Rear panel version (inner side)	With locking lugs
Rectangular shape	no
Base perforation	with base perforation
Halogen-free	yes
Cable retaining clip	no
Duct connector	no
Cover mounting type	Internal
Mounting perforation in base	yes
Usable cross-section	9950 mm ²
Cover supplied	no
Cover width	76.5 mm
ROHS-conformant	yes
Protection rating	IP30
Protective film	yes
Protection rating IK code	IK10
Symmetrical	no
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-25 °C