

Technical data sheet

Service pole, type ISSOGHS70140

Item number: 6289096



ISS aluminium service pole with a 76.5 mm system opening.

Set consists of:


1 single-compartment pole with stand

Total length: 675 mm

1 aluminium cover

Length: 675 mm

The design of this ISS service pole is based on the oval-shaped aluminium profile of ISSOG70140 floor-ceiling poles. The 76.5 mm system opening is suitable for directly accepting mounting box accessories of series 71GD... for the equipment with switching and connection devices.



Alu	Aluminium
EL	Anodised

Master data

Item number	6289096
Type	ISSOGHS70140EL
Description 1	Service pole
Description 2	floor
Manufacturer	OBO
Dimension	675x146x65
Colour	aluminium
Material	Aluminium
Surface	Anodised
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	220.5 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	22,7877 kg CO2e / 1 Piece


Technical data sheet

Service pole, type ISSOGHS70140

Item number: 6289096



Dimensions



Length	675 mm
Width	146 mm
Height	65 mm

Technical data

Number of usable covers	1
Number of compartments	1 St.
Version for	Single-sided
Fastening type	Stand
Floor mounting	yes
Ceiling mounting	no
Continuous profile	yes
Halogen-free	yes
Cable entry	Bottom
Cover width	76.5 mm
Changes according to location	no
Pole shape	Oval
Pole height, min.	675 mm
Adjustable	no
Pre-wired	no