

# Technical data sheet

Service pole, type ISSHS140500

Item number: 6290030




ISS aluminium service pole, 2-compartment, with a 76.5 mm system opening.

Empty, equippable with standard devices (socket, telephone, etc.) max. 8 devices.

Fixing possible directly on floor. Accessory mounting boxes to be ordered separately.

The service pole is suitable for accepting front-locking accessory mounting boxes of the series 71GD.... The installation of a partition of type GA-TW (6279711) and the installation of the cover clip, type KL80A, are possible as an option.



**Alu** Aluminium

## Master data

|                                    |                           |
|------------------------------------|---------------------------|
| Item number                        | 6290030                   |
| Type                               | ISSHS140500RW             |
| Description 1                      | Service pole              |
| Description 2                      | floor                     |
| Manufacturer                       | OBO                       |
| Dimension                          | 500x130x140               |
| Colour                             | Pure white; RAL 9010      |
| Material                           | Aluminium                 |
| Smallest sales unit                | 1                         |
| Unit of quantity                   | Piece                     |
| Weight                             | 302 kg                    |
| Weight unit                        | kg/100 pc.                |
| CO2 Footprint (GWP) Cradle-to-Gate | 38,5707 kg CO2e / 1 Piece |


# Technical data sheet

Service pole, type ISSHS140500

Item number: 6290030



## Dimensions



|        |        |
|--------|--------|
| Length | 500 mm |
| Width  | 130 mm |
| Height | 140 mm |

## Technical data

|                               |              |
|-------------------------------|--------------|
| Number of usable covers       | 2            |
| Number of compartments        | 2 St.        |
| Version for                   | Double-sided |
| Fastening type                | Bolts        |
| Floor mounting                | yes          |
| Ceiling mounting              | no           |
| Continuous profile            | yes          |
| Halogen-free                  | yes          |
| Cable entry                   | Bottom       |
| Cover width                   | 76.5 mm      |
| Changes according to location | no           |
| ROHS-conformant               | yes          |
| Pole shape                    | Rectangular  |
| Pole height, min.             | 500 mm       |
| Adjustable                    | no           |
| Pre-wired                     | no           |